



## Ethene, Ethylene Gas Sensor C2H4/S-1500-S

C2H4 Gas Sensor in Slim Housing

### **Applications**

- · Discontinuous Measurement
- Fruit Ripening

#### **Measurement**

Operation Principle	3-Electrode Electrochemical
Nominal Range	0 - 1500 ppm
Maximum Overload	3000 ppm
Inboard Filter	-
Output Signal	11 ± 5 nA/ppm
Resolution (Electronics dependent)	< 4 ppm
T80 Response Time	< 60 s
Typical Baseline Range (pure air, 20°C)	-10 ppm to 35 ppm
Maximum Zero Shift (+20°C to +40°C)	73 ppm
Repeatability	< 2 % of signal
Output Linearity	Linear
Gain (Only applies to 4-Electrode sensors)	-

Rev.: May-20 Page 1 of 4

Phone: +41 43 311 72 00 Fax: +41 43 311 72 01 E-Mail: info@membrapor.ch Website: www.membrapor.ch Membrapor AG Birkenweg 2 CH-8304 Wallisellen Switzerland

#### Performance data recorded at 20 - 25 °C, 30 - 50% RH, 900 - 1100 mbar





## Ethene, Ethylene Gas Sensor C2H4/S-1500-S

## **Electrical**

Rec. Load Resistor	10 - 33 Ω
Bias (V_Sens-V_Ref)	not recommended
Conformity to RoHS directive	RoHS Compliance

### **Environmental**

Relative Humidity Range	15 % to 90 % RH non-condensing
Temperature Range	-40 °C to 50 °C
Pressure Range	Atmospheric ± 10%
Pressure Coefficient	N.D.
Humidity Effect	None

## **Lifetime**

Expected Operation Life	2 years in air
Expected Long Term Output Drift in air	< 5 % signal loss per month
Filter Life	
Storage Life	6 months in container
Rec. Storage Temperature	5°C - 20°C
Warranty Period	12 months from date of dispatch

Rev.: May-20 Page 2 of 4

Phone: +41 43 311 72 00 Membrapor AG
Fax: +41 43 311 72 01 Birkenweg 2
E-Mail: info@membrapor.ch
Website: www.membrapor.ch
Switzerland


#### Performance data recorded at 20 - 25 °C, 30 - 50% RH, 900 - 1100 mbar





## Ethene, Ethylene Gas Sensor C2H4/S-1500-S

#### Slim-Size Outline Dimensions



### **Mechanical**

Weight 27 g

Orientation Any

Housing material Polycarbonate

Rev.: May-20 Page 3 of 4

Phone: +41 43 311 72 00

Fax: +41 43 311 72 01

E-Mail: info@membrapor.ch

Website: www.membrapor.ch

Website: www.membrapor.ch

Switzerland

### Performance data recorded at 20 - 25 °C, 30 - 50% RH, 900 - 1100 mbar





## Ethene, Ethylene Gas Sensor C2H4/S-1500-S

## **Cross Sensitivity Data**

The table below does not claim to be complete. Interfering gases should not be used for calibration. Please contact Membrapor AG for further support regarding cross sensitivities.

Interfering Gas Cross-Sens. [%]

CO < 60

Rev.: May-20 Page 4 of 4

Phone: +41 43 311 72 00 Fax: +41 43 311 72 01 E-Mail: info@membrapor.ch Website: www.membrapor.ch Membrapor AG Birkenweg 2 CH-8304 Wallisellen Switzerland

#### Performance data recorded at 20 - 25 °C, 30 - 50% RH, 900 - 1100 mbar